# Drum Containment System DCS® Filling





- Contained drum and big bag filling
- Operator, product and environment protection
- Safe handling of toxic or explosive powders
- Adaptable to empty any type of process equipment
- Primary and secondary containment
- Compact and low height system
- Ergonomic













Easy Cleaning

орелию

**Powder Handling Excellence** 

## Drum Containment System DCS® Filling



The patented DCS® Drum Containment System allows contamination free filling of drums of various sizes comprising single or double liners under high containment (< 1µg/m3). The DCS® can be installed on load cells to ensure precise filling of drums.

This space saving device can be easily connected below the process equipment to be discharged, it can also be installed in a remote place in case of lacking head room below the equipment or when a number of process equipment are to be emptied through one single filling station.

The modular system can be designed to fill both drums with liners and big bags. It can also be combined with the MPTS Sampling Device for taking samples during the filling process.

With safety always a priority, the DCS® guarantees both primary and secondary containment, with a glove box enabling the

operator to connect the drum liners within a sealed environment.

The fully cleanable DCS® system features a Push-Push HEPA filter which is connected to an extraction system. System available in various materials (SS, HC22, Halar coated, etc.) and on load cells. Inertisation possible. Appropriate for use in ATEX zone 1/21.

## Design

- AISI type 316L stainless steel, electro-polished
- Other materials available (SS, HC22, Halar coated, etc.)
- · Push-Push HEPA filter
- ATEX zone 1/21


### Features

- Contamination free filling of drums of various sizes with double liners
- Filling of standard or custom made big bags
- Filling by gravity

- Filling in combination with a PTS
   Powder Transfer System if headroom
   limited
- High containment (<1µg/m3)</li>
- Single filling station for multiple discharge points
- · Primary and secondary containment
- Containment not required during operation
- · High system visibility
- · Space saving
- Simple to install
- Easy to clean
- GMP compliant, ISO 6 class internal

### Options

- · Load cells for accurate dosing
- · Inert operation
- Combined station for big bag and drum filling
- Viable for sampling
- Adaptable to nanogram level containment  $< 0.1 \mu g/m3$
- ATEX zone 1/21



Dec Group Headquarters: Dietrich Engineering Consultants sa · Z.I. Larges Pièces A · Ch. du Dévent · P.O. Box 9 1024 Ecublens/Lausanne · Switzerland · Tel +41 21 /694 20 40 · Fax +41 21 /694 20 59 · info@dec-group.net